




Home of Containment Solutions



TransferBag System

Containment-Level \leq OEB 5 ($<1\mu\text{g}/\text{m}^3$)



LUGAIA
Containment solutions



SafePort TransferBag (patented)

Contamination-Free Product Transfer

Design of the SafePort TransferBags

The **Lugaia SafePortBag** offers a combination of low investment costs and high containment levels. The disposable version is suitable for safe product transfers according to the containment level of OEB 5 ($<1\mu\text{g} / \text{m}^3$).

Components:

- 1 SafePort Connector
- 2 Extractors
- 3 Side locking clip
- 4 SafePort TransferBag
- 5 SafeStick with security lock
- 6 SafePort Initial flange
- 7 SafePort connecting head

Connection Options:

- SafePort inlet and outlet
- O-ring inlet, SafePort outlet
- Open inlet, SafePort outlet
- TriClamp inlet, SafePort outlet


Standard Sizes

Volume Content (l)	Bag Width (mm)	Bag Length (mm)
SafePort Bag		
5	300	1100
25	500	1300
40	600	1500
Drumbag		
180	550	1300

Special sizes available on request!



Scan the QR code for a direct animation.



SafePort TransferBag (patented)

Contamination-Free Product Transfer

SafePort TransferBag and Drumbag

Contents vary from 5 to 180 liters



SafePort TransferBag, 5 to 40 liters



Drumbag, 180 liters



SafePort connecting head with integrated CIP System



Protective cover for SafePort System



Scope of delivery:

- 1 SafePort Bag
- 2 SafeStick
- 3 Mounting Aid
- 4 SafePort Connecting Head
- 5 Protective cover
- 6 CIP Adapter (optional)
- 7 Initial flange

SafePort TransferBag (patented)

Contamination-Free Product Transfer

With SafePort TransferBag system, products can be safely transferred with containment level OEB 5. The special SafePort connection enables continuous connecting of bags for repeated product feed without interrupting the containment. This guarantees a very high yield for your products.

The advantages of SafePort TransferBag:

- Inexpensive, disposable version for a safe transfer in the OEB 5 (<math><1\mu\text{g}</math> / m³) containment level
- Clean room production according to "state of the art" guidelines with USP / EP certificates ISO 8/7/5
- Special designs with sampling sleeve and customer specific foils available
- Contents can be selected from 5-40 liters to 180 liters (special sizes on request)
- No product is lost when emptying thanks to a special connection system with a completely free cross-section inside
- Lower investment costs compared to rigid systems
- Simple and safe connection system for feeding multiple products
- Optional cleaning system is available

SafePortBag Subsequent Assembly



Docking the SafePortBag



Removing the remaining piece



Emptying the SafePortBag



Closing the SafePortBag using the SafeSeal System



Separation of the SafePortBag using the SafeSeal System



Attaching the protective cover

SafeStick Closure System


SafeStick and fuse clips

SafeStick – easy to close

With the SafeStick, Lugaia Containment Solutions guarantees a safe, inexpensive, and simple closure element for TransferBags for all types and sizes.

The Advantages of SafeStick:

- Completely made of PE
- Guaranteed tightness due to the omega profil
- Available in different lengths
- Can be used for all bags
- Easy Handling
- High occupational safety
- Universally applicable
- High quality
- Inexpensive



Montage Installation of SafeStick and fuse clips



Press the round rod into the omega profile



Attach the Safety lock



TransferBag

Product transfers for small quantities



TriClamp-Locking / Connection options:

- 1 TriClamp closure size 4"
- 2 TriClamp closure size 6"
- 3 Associated blind lids for tight sealing



The advantages of the TransferBag:


- Optimal connection options
- Different sizes
- Custom foils available at any time
- Meets the high requirements in the pharmaceutical and biotech industries
- Custom design and execution

The Lugaia TransferBags can be used for powder transfers of small quantities while meeting the high requirements in the pharmaceutical and biotech industries. On request, the bags can be made from customer-specific

foil in the three clean room classes: ISO 5, ISO 7 and ISO 8. Customized designs for the TransferBags with various connection options are also available.

TransferBag

Configuration options



Connection options can be put together individually depending on the requirements.


Volume-content (l)	Bag width B1 (mm)	Bag length L (mm)	TriClamp-Connection (*)	Ø-Connection tube for O-Ring (mm)
5	400	400	4" / 6" / DN150	170
10	400	700	4" / 6" / DN150	170
15	400	1100	4" / 6" / DN150	170
20	500	1100	4" / 6" / DN150	230
25	500	1400	4" / 6" / DN150	230
30	700	1200	4" / 6" / DN150	230
40	700	1600	4" / 6" / DN150	230

(Special sizes available on request)

Various Configuration Options



Configuration Options





Lugaia AG
Containment Solutions

Industriezone Basper 31
3942 Raron, Switzerland
Telephone +41 (0) 27 948 45 55
Telefax +41 (0) 27 948 45 50
anfrage@lugaia.ch

Lugaia Deutschland GmbH
Containment Solutions

Westendstraße 2
85084 Reichertshofen, Germany
Telephone +49 (0) 8453 33 550-0
Telefax +49 (0) 8453 33 550-99
info@lugaia.de

Lugaia USA, LLC
Containment Solutions

Ponte Vedra Beach, Florida
Telephone +1 904 401 0003
info@lugaia.com

www.lugaia.com

Our product overview:

- CLS – Continuous Liner System
- Liner Carrier Systems
- SafeSeal Closure System
- SafePort TransferBag
- TransferBag
- SafeFlex Isolators
- Individual special solutions

follow us on

